


RANGE 3/5 NF EN ISO 1182

SAFETY STORAGE CABINETS

for Toxic, Noxious or Flammable products

**DIRECTIVES & NORMS**

- In as per EN ISO 1182.
- Normalized labelling according to ISO 3864 norm and 92/58/CEE directive.

ADVANTAGES

- Large storage capacity.
- Cabinets for various families of products storage (noxious, toxics and flammables) with same design for a better homogeneity.

PASSIVE SECURITY

- Built in double wall steel 12/10th.
- 20 mm thickness of mineral fibre insulation.
- White epoxy paint RAL 9010.
- «Toxics», «Noxious» or «Flammables» large warning label.
- Adjustable containment shelves.

ACTIVE SECURITY

- Inside lateral ventilation shaft with high opening and connecting piece (Ø 100 mm).
- Ventilation outlet on the roof with connecting sleeve (Ø 100 mm).
- Reinforced gate hook, sealing off by 2 points lock.
- Key locking.

OPTIONS

- Additional retention shelf (G03, G04 or G06).
- Containment shelf in PVC (EP03, EP04 or EP06).
- Base through in steel (GL03, GL04, or GL06).
- Base through in PVC (BP03, BP04 or BP06).
- Absorbing carpets (ref. JF10).

**ADDITIONAL EQUIPMENT OF THE RANGE 5**

- Removable base through in steel at the bottom.
- Self closing system of the doors.
- Opening vent with fusible link.

RANGE 5 OPTIONS

- Open doors locking system with self closing system at 70°C.
- Additional retention shelf (G03, G04 ou G06).
- Containment shelf in PVC (EP03, EP04 ou EP06).
- Containment sump in PVC (BP03, BP04 ou BP06).


Ventilation and Filtration Boxes

To protect the users health and to improve the life cycle of your safety cabinet, we recommend to install an exhausting system. Do not hesitate to contact-us for more information.



RANGE 3/5

NF EN ISO 1182



RANGE 3

| P/N | Description | Outside dim. H x W x D (mm) | Inside dim. H x W x D (mm) | Storage capacity (L) | Number of shelves | Maximum load by shelf ⁽¹⁾ (kg) | W. (kg) |
|--------|---------------------------------------|--------------------------------|-------------------------------|-------------------------|----------------------|--|------------|
| SV50 | Under-bench cabinet (depth: 450 mm) | 750 x 1000 x 450 | 650 x 950 x 400 | 50 | 1 | 75 | 62 |
| G803G | Low cabinet (depth: 300 mm) | 895 x 1000 x 300 | 745 x 950 x 250 | 70 | 1 | 75 | 58 |
| G804G | Low cabinet (depth: 450 mm) | 895 x 1000 x 450 | 745 x 950 x 400 | 100 | 1 | 75 | 68 |
| G806G | Low cabinet (depth: 600 mm) | 895 x 1000 x 600 | 745 x 950 x 550 | 135 | 1 | 75 | 82 |
| G1204E | Working cover cabinet (depth: 450 mm) | 1205 x 1000 x 450 | 1145 x 950 x 400 | 150 | 3 | 75 | 92 |
| G2004B | Tall cabinet (depth: 450 mm) | 2095 x 1000 x 450 | 1945 x 950 x 400 | 250 | 5 | 75 | 145 |
| G2006B | Tall cabinet (depth: 600 mm) | 2095 x 1000 x 600 | 1945 x 950 x 550 | 300 | 5 | 75 | 166 |

RANGE 5

| P/N | Description | Outside dim. H x W x D (mm) | Inside dim. H x W x D (mm) | Storage capacity (L) | Number of shelves | Maximum load by shelf ⁽¹⁾ (kg) | W. (kg) |
|--------|---------------------------------------|--------------------------------|-------------------------------|-------------------------|----------------------|--|------------|
| S604T | Under-bench cabinet (depth: 450 mm) | 750 x 1000 x 450 | 650 x 950 x 400 | 50 | 1 | 75 | 69 |
| S804T | Low cabinet (depth: 450 mm) | 895 x 1000 x 450 | 745 x 950 x 400 | 100 | 1 | 75 | 75 |
| S806T | Low cabinet (depth: 600 mm) | 895 x 1000 x 600 | 745 x 950 x 550 | 135 | 1 | 75 | 90 |
| S1204T | Working cover cabinet (depth: 450 mm) | 1205 x 1000 x 450 | 1145 x 950 x 400 | 150 | 3 | 75 | 99 |
| S2004T | Tall cabinet (depth: 450 mm) | 2095 x 1000 x 450 | 1945 x 950 x 400 | 250 | 5 | 75 | 152 |
| S2006T | Tall cabinet (depth: 600 mm) | 2095 x 1000 x 600 | 1945 x 950 x 550 | 300 | 5 | 75 | 174 |

OPTIONS

| P/N | Description | W. (kg) |
|------|--|------------|
| G03 | Additional shelf for G803G | 3 |
| G04 | Additional shelf for SV50-G804G-G1204E-G2004B-S604T-S804T-S1204T-S2004T | 4 |
| G06 | Additional shelf for G806G-G2006B-S806T-S2006T | 5 |
| EP03 | Containment shelf in PVC for G803G | 6 |
| EP04 | Containment shelf in PVC for SV50-G804G-G1204E-G2004B-S604T-S1204T-S2004T | 6 |
| EP06 | Containment shelf in PVC for G806G-G2006B-S806T-S2006T | 6 |
| GL03 | Containment sump for G803G | 4 |
| GL04 | Containment sump for SV50-G804G-G1204E-G2004B-S604T-S1204T-S2004T | 5 |
| GL06 | Containment sump for G806G-G2006B-S806T-S2006T | 6 |
| BP03 | Containment sump in PVC for G803G | 3 |
| BP04 | Containment sump in PVC for SV50-G804G-G1204E-G2004B-S604T-S1204T-S2004T | 4 |
| BP06 | Containment sump in PVC for G806G-G2006B-S806T-S2006T | 5 |
| FTR5 | Self closing system at 70°C with open doors locking system (must be ordered together with the cabinet) | |

⁽¹⁾ Evenly distributed ⁽²⁾ In option: height 670 mm. Contact-us for more information.

The manufacturer reserves the right to discontinue or change specifications or designs at any time without notice and without incurring obligations. 05/2017

Flammable
cabinets

Corrosive
cabinets

Toxic cabinets
and multirisk

Pesticide
range

Fume hoods, filtering
cabinets - Ventilation

Containment
and Cans

File cabinets
Anti-fire equipments

Showers and first-
aid equipments